

Video microscope KERN OIV-2





OIV 254 Snapshot button

The comprehensive digital solution for increased working comfort when carrying out continuous monitoring work in industry.

Features

- The Kern OIV-2 is a video microscope which has been constructed to optimise digital stereo microscopy. Our well-conceived, comprehensive solution with axial optical unit enables immediate, simple display of your samples on the screen.
- The LED incident illumination unit (ring) included as standard guarantees the very best illumination of your sample.
- Combined with the large working surface, recording objects on the screen is ideally suited for monitoring, analysis and documentation in industrial environments.
- The excellent optical unit enables continuous sharp image tracking across the entire zoom range from 0.7×-5×.
- The powerful 2.0 megapixel camera of the microscope without eyepieces offers, thanks to the HDMI output, smooth live monitoring of your samples from the HD monitor. In addition, the software which is easy to use, the USB stick as well as the USB mouse which are integral components of the delivery, mean you can process and store your results digitally.
- With the OIV 254 model, there is the option of image capture at the push of a button, without having to detour via the software.
 Whereas the OIV 255 guarantees software-controlled taking of images and videos with additional, documentation functions
- A protective dust cover, as well as multi-lingual user instructions are included in the scope of the delivery

Technical data

- Optical system: Axial
- · Brightness adjustable
- Screen: 12", 1920×1080 HD,
 -5°-15° inclination
- Magnification ratio: 7,1:1
- Stand: arm curved
- Illumination: 2 W LED ring (incident)
- Data storage: External using USB (Max 128 GB)
- · Working distance: 105 mm
- Maximum sample height: 100 mm
- Overall dimensions W×D×H 320×260×483 mm
- Net weight approx. 6 kg

Accessories

 Auxiliary objective 0,5×, KERN OZB-A2101

STANDARD



Model	Standard configuration						
	Resolution	Interface	Sensor	Field of view	Objective	Software functions	
KERN	camera			mm	Zoom		
OIV 254	2 MP	HDMI (60 FPS)	CMOS 1/2"	Ø 29,82-4,18	0,7×-5×	Image capture	
OIV 255	2 MP	HDMI (60 FPS)	CMOS 1/2"	Ø 29,82-4,18	0,7×-5×	Images and videos, documentation	



Pictograms



360° rotatable microscope head



Monocular Microscope

For the inspection with one eye



Binocular Microscope

For the inspection with both eyes



Trinocular Microscope

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination

For pictures bright and rich in contrast



LED illumination

Cold, energy-saving and especially long-life illumination



Incident illumination

For non-transparent objects



Transmitting illumination

For transparent objects



Fluorescence illumination

For stereomicroscopes



Fluorescence illumination

for compound microscopes

With 100W mercury lamp and filter



Fluorescence illumination for compound microscopes

With 3 W LED illumination and filter



Phase contrast unit For a higher contrast



Darkfield condenser/unit

For a higher contrast due to indirect illumination



Polarising unit

To polarise the light



Infinity system

Infinity corrected optical system



Zoom magnification For stereomicroscopes



Auto-focus

For automatic control of the focus level



Parallel optical system

For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD card





USB 2.0 digital camera



LWD

For direct transmitting of the picture to a PC



USB 3.0 digital camera

For direct transmitting of the picture to a PC



WLAN data interface

For transmitting of the picture to a mobile display device



HDMI digital camera

For direct transmitting of the picture to a display



PC software

To transfer the measurements from the device to a PC



Automatic temperature compesation

For measurements between 10 °C and 30 °C



Protection against dust and water splashes

IPxx: The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013



Battery operation

Ready for battery operation. The battery type is specified for each device.



Battery operation rechargeable

Prepared for a rechargeable battery operation



Plug-in power supply

230V/50Hz in standard version for EU. On request GB, AUS or USA version.



Integrated power supply unit

Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.

Abbreviations

Adapter for the connection of a C-Mount

Frames per second

camera to a trinocular microscope

SWF

Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)

N.A. Numerical Aperture

Working Distance W.D.

H(S)WF

FPS

High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses)

SLR camera Single-Lens Reflex camera

Long Working Distance

WF

Wide Field (Field number up to Ø 22 mm for 10× eyepiece)

Your KERN specialist dealer: