Temperature calibrator TP M255S

TP Solid // Calibration bath // Room temperature...255 °C // RT...491 °F





Highlights

- · Very easy operation with 4-button control and integrated reference temperature sensor
- PC interface with connection cable to USB for use with SIKA calibration software
- · Low weight and stable handle for easy transport
- Optional accessory: Transport case with or without trolley
- · Qualified for SIKA Gold Service
- Especially suitable for calibration of devices under test with special sensor geometry. DUTs are simply immersed in the calibration liquid, no calibration insert with specific bore hole pattern is required.

TP Solid

With the temperature calibrators of the TP Solid series, the main focus is on **flexibility**: In addition to **dry block calibrators**, they also include **calibration baths**, with which almost any temperature sensor can be calibrated irrespective of its shape. Both can be operated **easily and intuitively**. When being used as fluid bath calibrator, the temperature sensors are directly immersed into the calibration liquid. This creates a direct temperature link

between the calibrator and the devices under test without insulating air gap. All TP Solid temperature calibrators are additionally equipped with a **serial interface for computer-assisted monitoring** of the calibration process. This flexibility in combination with the easy operation make the TP Solid series ideal for **use in machinery and plant engineering**.

SIKA temperature calibrators

Temperature calibrators are used for the verification of the functionality and calibration of temperature measuring devices and temperature sensors. As the sole German manufacturer of these devices, we develop and produce our "Made in Germany" temperature calibrators with a special focus on long-term reliability and utmost accuracy in combination with easy operation. We can rely on more than 40 years of experience in doing this: SIKA's first dry block temperature calibrator was launched all the way back in 1980.

Every SIKA temperature calibrator is meticulously tested for accuracy and stability. This is attested by our standard calibration certificate, which we issue with every temperature calibrator, or by means of an optional DAkkS calibration certificate [German accreditation body]. This is to guarantee that you receive a perfect product which can be traced back to national and international temperature measurement standards.

SIKA Dr. Siebert & Kühn GmbH & Co. KG Struthweg 7-9 // 34260 Kaufungen // Germany www.sika.net

Features

Easy operation

- The TP M255S can be operated with only four buttons:
 Two arrow buttons for setting the target temperature,
 one button for confirmation and one return button
- Thus, temperatures can be set as easily as, for example, in the air conditioning system in your car
- Any operational errors can be nearly excluded. You do not need any specifically trained staff or time-consuming briefings



SIKA Gold Service

SIKA Gold Service provides a comprehensive service package for the regular recalibration of your temperature calibrator. You will benefit from exclusive savings and discounts as well as special promotions reserved to SIKA Gold Service members.

- You will save 33% in the recalibration of your temperature calibrator
- You will receive a 10% discount on any repairs that may become necessary
- You will receive preferential invitations to product presentations, symposia, practice days and exclusive training offers

Register now and benefit from the SIKA Gold Service: gold-service.sika.net





Technical data

TP M255S		
Temperature range	Room temperature255 °C	Room temperature491 °F
Calibration volume	Ø 60 x 170 mm	
Calibration bath		
Accuracy	±0.2 °C	±0.36 °F
Temperature stability	±0.05 °C	±0.09 °F
Resolution of the temperature display	0.01 °C in the range -9.9999.99 °C, else 0.1 °C	0.01 °F in the range -9.9999.99 °F, else 0.1 °F
Reference temperature sensor	internal, fixed installation	
Interface	RS485 (calibrator) to USB (PC)	
Connectivity	MODBUS	
Dimensions		
→ Width	150 mm	
→ Height	330 + 70 mm	
→ Depth	270 mm	
Weight	Approx. 7.5 kg	
Power supply	110115 V 60 Hz / 230 V 50 Hz	
Power consumption	Approx. 1000 W	
Display		
Display	2-line, 4-digit digital display, red / green, unit °C	/ °F
Approvals		
	CE ROHS REACH EF	

Technical datasheet

10/2023 // V1.2 3 // 5

Article numbers

To order a complete calibrator, you need two article numbers:

- 1. Calibrator
- 2. Calibration insert

In addition, depending on your individual calibration requirements, you can order additional calibration inserts, necessary certificates and other accessories.

1. Calibrator								
Temperature range		Function	Calibration insert [mm]	Power supply	Article number			
Room temperature255 °C	RT491 °F	Calibration bath	Ø 60 x 170	100230 V	EPMB250S601503			

Notice: Every "linearisation" article number with 13 digits starts with "EK1", while the following letters ("short designation") indicate the selected calibration function. You may also select several functions of one category. Please indicate the calibration functions in alphabetical order and fill in any possibly remaining positions with "0".

2. Linearisation												
Calibration functi	on		Calibration insert / calibration medium			Reference temperature sensor			Short designation			
Calibration bath (Direct filling)		20 cSt	7220 °C	4	4.6428 °	°F	internal		R			
		50 cSt	St 50270 °C		122518 °F internal		internal			Т		
Example article number linearisation												
Function:		1	2	3	4	5		6	7	8	9	10
Article number:	EK1	Т	0	0	0	0		0	0	0	0	0

3. Calibration certificate - Select your calibration certificates as needed Each calibrator is already delivered with a standard calibration certificate (3 test points).	Article number
SIKA works calibration certificate (similar to standard certificate + marking on the calibrator), 1st calibrator function	EKTPWP1FKT
SIKA works calibration certificate (similar to standard certificate + marking on the calibrator), 2nd calibrator function	EKTPWP2FKT
DAkkS calibration certificate (3 test points + measurement uncertainty determination) for 1st calibrator function	EKTPDAKKS1FKT
DAkkS calibration certificate (3 test points + measurement uncertainty determination) for 2nd calibrator function	EKTPDAKKS2FKT
Each additional test point DAkkS calibration certificate	EKTPDAKKSZUSP
SIKA Gold Service works calibration certificate	EKTPGOLDWP
SIKA Gold Service DAkkS	EKTPGOLDDAKKS

4. Accessories	Article number
Transport case without trolley	EZTPKOFFER20
Transport case with trolley	EZTPKOFFER20TG
Tripod (holder for devices under test)	EZTPMSG0000000
Calibration liquid (silicone oil), 50cSt	EZSÖ0500000000
PC software	EZ9999999971
PC connection cable: temperature calibrator (RS485) to USB	EZ17000000002

SIKA Dr. Siebert & Kühn GmbH & Co. KG
Struthweg 7-9 // 34260 Kaufungen // Germany
www.sika.net

Technical datasheet

10/2023 // V1.2 4 // 5

Overview of SIKA temperature calibrators

Our series: Basic. Solid. Premium.

- Dry block calibrators of the TP Basic series impress with their uncomplicated operation and high cost-effectiveness.
 They are particularly suitable for use on ships or in industrial applications.
- Equipped with a PC interface, the dry block calibrators and calibration baths of the TP Solid series cover a wide temperature range with high accuracy.
- For the highest demands on accuracy and flexibility:
 The dry-block and multi-function temperature calibrators of the TP Premium series represent the pinnacle of our technical development. Equipped with an integrated touch screen, a PC interface, an external reference sensor and integrated measuring instrument, this series offers extreme accuracies for all calibration tasks.

Temperature range (RT=Room temperature)	Function	Accuracy		Features	Block dimensions [Ø mm x depth mm]	Туре	
FF *0	Dry block	±0.4 °C	±0.72 °F	TP Basic	28 x 150	TP 17200	
-55 °C 200 °C -67 °F 392 °F	Dry block	±0.2 °C	±0.36 °F	TP Solid	28 x 150	TP 17200S	
-0/ F 392 F	Dry block	±0.2 °C	±0.36 °F	TP Premium	28 x 150	TP 37200E.2	
-35 °C 155 °C -31 °F 311 °F	Calibration bath	±0.1 °C	±0.18 °F	TP Solid	60 x 170	TP M165S	
	Dry block	±1 °C	±1.80 °F	TP Basic	28 x 150	TP 17165M	
	Dry block	±0.4 °C	±0.72 °F	TP Basic	28 x 150	TP 17165	
	Dry block	±0.2 °C	±0.36 °F	TP Solid	28 x 150	TP 17165S	
	Dry block	±0.2 °C	±0.36 °F	TP Premium	28 x 150	TP 37165E.2	
-35 °C 165 °C	Dry block ext.	±0.2 °C	±0.36 °F				
-31 °F 329 °F	Dry block int.	±0.3 °C	±0.54 °F				
	Air Shield Insert	±0.07 °C	±0.126 °F	TP Premium	60 x 170	TP 3M165E.2	
	Calibration bath	±0.1 °C	±0.18 °F	TI TICITII GITT	00 x 170	11 31111032.2	
	Infrared	±0.5 °C	±0.9 °F				
	Surface	±1 °C	±1.88 °F				
-30 °C 165 °C	Dry block	±0.4 °C	±0.72 °F	TP Basic	60 x 150	TP 17166	
-22 °F 329 °F	Dry block	±0.2 °C	±0.36 °F	TP Solid	60 x 150	TP 17166S	
-10 °C 100 °C 14 °F 212 °F	Dry block	±0.05 °C	±0.09 °F	TP Solid	7 x 6.5 x 150	TP 17Zero	
RT 200 °C RT 392 °F	Dry block	±1 °C	±1.80 °F	TP Basic	18 x 150	TP 18200E	
	Calibration bath	±0.2 °C	±0.36 °F	TP Solid	60 x 170	TP M255S	
RT 255 °C RT 491 °F	Dry block ext. Dry block int. Air Shield Insert Calibration bath, tub insert, ext. Calibration bath, tub insert, int. Calibration bath, direct filling, ext. Calibration bath, direct filling, int. Infrared Surface	±0.25 °C ±0.5 °C ±0.08 °C ±0.35 °C ±0.53 °C ±0.18 °C ±0.46 °C ±0.5 °C ±1 °C	±0.45 °F ±0.9 °F ±0.144 °F ±0.63 °F ±0.954 °F ±0.828 °F ±0.9 °F ±1.8 °F	TP Premium	60 x 170	TP 3M255E.2	
	Dry block	±0.6 °C	±1.08 °F	TP Basic	60 x 150	TP 17450	
	Dry block	±0.3 °C	±0.54 °F	TP Solid	60 x 150	TP 17450S	
RT 450 °C RT 842 °F	Dry block Air Shield Insert Infrared Surface	±0.3 °C ±0.2 °C ±0.5 °C ±1 °C	±0.54 °F ±0.36 °F ±0.9 °F ±1.8 °F	TP Premium	60 x 150	TP 37450E.2	
	Dry block	±1 °C	±1.8 °F	TP Basic	28 x 150	TP 17650M	
RT 650 °C RT 1202 °F	Dry block	±0.8 °C	±1.44 °F	TP Basic	28 x 150	TP 17650	
	Dry block	±0.4 °C	±0.72 °F	TP Solid	28 x 150	TP 17650S	
RT 700 °C	Dry block	±0.43 °C	±0.744 °F				
RT 1292 °F	Air Shield Insert	±0.27 °C	±0.486 °F	TP Premium	29 x 150	TP 37700E.2	
RT 850 °C RT 1562 °F	Dry block	±1 °C	±1.8 °F	TP Basic	18 x 100	TP 18850E	
400 °C 1300 °C 752 °F 2372 °F	Dry block	±2 °C	±3.6 °F	TP Solid	28 x 200	TP 281300E	

Subject to technical modifications and errors

SIKA Dr. Siebert & Kühn GmbH & Co. KG Struthweg 7-9 // 34260 Kaufungen // Germany www.sika.net